



Main

| | |
|---------------------------|---|
| Range | Neo |
| Product or component type | Control switch |
| Wiring device mounting | Flush Surface |
| Switch function | 2-way |
| Switch application | Switch |
| Load type | Fluorescent lamp Incandescent lamp Inductive Resistive |
| Bulb type | Fluorescent with white |
| Colour tint | White |

Complementary

| | |
|------------------------------|--|
| Rated current | 10 A, 250 V, AC, 50/60 Hz |
| Number of gangs | 2 gangs horizontal |
| Material | Brass metal parts Polycarbonate plastic part Steel metal parts |
| Clamping connection capacity | 3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s) |
| Connections - terminals | Pillar terminals |
| Width | 87 mm |
| Height | 87 mm |
| Embedding depth | 23.5 mm |
| Depth | 36 mm |

Environment

| | |
|---------------------------------------|---|
| Ambient air temperature for operation | 0...40 °C |
| Relative humidity | 0...95 % |
| Environmental characteristic | Indoor use |
| Standards | EN 60669-1 GB 16915.1 IEC 60669-1 |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 1809 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Need no specific recycling operations |