

Product data sheet

Specifications



Dual Telecommunication Outlets (Tel. RJ11 + Data RJ45), Grey Silver

E3032TD_GS

Main

| | |
|---------------------------|-----------------------|
| Range | Neo C-Metro |
| Product Or Component Type | Data/telephone socket |
| Colour Tint | Grey silver |

Complementary

| | |
|--------------------------------|---|
| Rated Current | 1.5 A at 125 Vrms AC |
| Communication Network Category | Voice: 3e Data: 5e |
| Insulation Resistance | >= 1000 MOhm for voice >= 200 mOhm for data |
| Contact Resistance | Data: 1000 µOhm Voice: 100000 µOhm |
| Number Of Gangs | 2 gangs |
| Minimum Return Loss | 23 dB |
| Awg Gauge | Data: AWG 26...AWG 22(4 twisted pair cables) Voice: AWG 26...AWG 24(2 twisted pair cables) |
| Contacts Material | Contact: phosphor bronze for voice module Contact: phosphor bronze with gold plating for data module IDC contact: phosphor bronze with nickel plating for data module IDC contact: phosphor bronze with tin plating for voice module |
| Material | Voice: PBT 15 % FG insert PC housing Polycarbonate plastic part |
| Device Mounting | Surface Flush |
| Width | 87 mm |
| Height | 87 mm |
| Depth | 36 mm |
| Embedding Depth | 28.4 mm |

Environment

| | |
|---------------------------------------|--|
| Dielectric Strength | Data: 1000 V for 60 s at 60 Hz Voice: 750 V for 60 s at 60 Hz |
| Ambient Air Temperature For Operation | 0...40 °C |
| Relative Humidity | 0...95 % |
| Environmental Characteristic | Indoor use |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-----------|--|
| Standards | EIA/TIA 568 FCC part 68 ISO/IEC 11801 YD/T 577-92 |
|-----------|--|

Packing Units

| | |
|------------------------------|--------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.6 cm |
| Package 1 Width | 8.7 cm |
| Package 1 Length | 8.7 cm |
| Package 1 Weight | 92 g |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 8 |
| Package 2 Height | 15 cm |
| Package 2 Width | 19 cm |
| Package 2 Length | 8 cm |
| Package 2 Weight | 750 g |
| Unit Type Of Package 3 | CAR |
| Number Of Units In Package 3 | 80 |
| Package 3 Height | 21 cm |
| Package 3 Width | 31 cm |
| Package 3 Length | 50 cm |
| Package 3 Weight | 8500 g |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Compliant with Exemptions

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations