

Product data sheet

Specifications



13A 250V 1 Gang Switched Socket, White

E8215_WE

Main

Product Or Component Type	Socket-outlet
Switch Function	Switch
Rated Current	13 A at 250 V AC 50...60 Hz
Number Of Gangs	1 gang
Load Type	Resistive
Cover Frame Colour Tint	White

Complementary

Wiring Device Mounting	Flush Surface
Material	Polycarbonate: surround Polycarbonate: grid plate
Clamping Connection Capacity	2 x 4 mm² for stranded cable(s) 3 x 2.5 mm² for solid cable(s)
Width	87 mm
Height	87 mm
Depth	26.6 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	BS 1363-2 SS 145-2 MS 589-2

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.7 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	108 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	824 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	80
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	8638.64 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation