

Product data sheet

Specifications



Double USB charger, AvatarOn type A, 2.1A, White

E8332USB_WE_G11

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Product Or Component Type	USB charger
Integrated Connection Type	2 USB type A 5 V DC, maximum load current: 2.1 A

Complementary

Device Mounting	Flush
Device Presentation	Complete product
Colour Tint	White
Surface Finish	Glossy
[Ue] Rated Operational Voltage	100/240 V AC 50/60 Hz
Maximum Load Current With 2 Outputs Used Simultaneously	2.1 A
Material	PC (polycarbonate)
Connections - Terminals	Screw terminals
Screwdriver Shape	Phillips combined
Clamping Connection Capacity	1.5...2.5 mm ² for flexible cable(s) 1.5...2.5 mm ² for rigid cable(s)
Height	86 mm
Width	86 mm
Depth	40 mm

Environment

Standards	IEC 60950-1
Electrical Insulation Class	Class II
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	100 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	19 cm
Package 2 Length	19.5 cm
Package 2 Weight	880 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	48
Package 3 Height	21 cm
Package 3 Width	30 cm
Package 3 Length	39.5 cm
Package 3 Weight	5.28 kg

Sustainability


Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)