

# Product data sheet

Specifications



## 4 Switch, AvatarOn, 1-pole 1-way, brass terminal, IP20, wine gold

E8334L1\_WG\_C5

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

|                           |   |
|---------------------------|---|
| Product Or Component Type | Switch  |
| Device Application        | Control   |
| Load Type                 | Inductive<br>Fluorescent lamp<br>Incandescent lamp<br>Resistive |
| Colour Tint               | Wine gold   |

### Complementary

|                              |  |
|------------------------------|--|
| Device Presentation          | Complete product   |
| Rated Current                | 16 AX at 250 V AC 50/60 Hz   |
| Switch Function              | 1-pole 1-way   |
| Number Of Gangs              | 4 gangs  |
| Number Of Rocker             | 4  |
| Clamping Connection Capacity | 3 x 2.5 mm <sup>2</sup> for solid cable(s)<br>3 x 2.5 mm <sup>2</sup> for stranded cable(s)<br>4 x 1.5 mm <sup>2</sup> for solid cable(s)<br>4 x 1.5 mm <sup>2</sup> for stranded cable(s) |
| Connections - Terminals      | Brass terminal   |
| Material                     | Polycarbonate: grid plate<br>Polycarbonate: base<br>Polycarbonate: dolly<br>Polycarbonate: frame<br>Polycarbonate + GF 20 %: actuator  |
| Device Mounting              | Surface<br>Flush   |
| Width                        | 86 mm  |
| Height                       | 86 mm  |
| Depth                        | 34.2 mm  |

### Environment

|   |              |
|---|--------------|
| Ip Degree Of Protection                       | IP20         |
| Maximum Ambient Air Temperature For Operation | 45 °C        |
| Operating Altitude                            | 2000 m       |
| Relative Humidity                             | 0...95 %     |
| Environmental Characteristic                  | UV resistant |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|           |  |
|-----------|--|
| Standards | BS EN 60669-1<br>MS IEC 60669-1<br>SS 227-1<br>IEC 60669-1 |
|-----------|--|

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 3.4 cm   |
| Package 1 Width              | 8.6 cm   |
| Package 1 Length             | 8.6 cm   |
| Package 1 Weight             | 128.0 g  |
| Unit Type Of Package 2       | CAR      |
| Number Of Units In Package 2 | 8        |
| Package 2 Height             | 9.5 cm   |
| Package 2 Width              | 19.0 cm  |
| Package 2 Length             | 19.5 cm  |
| Package 2 Weight             | 1128.0 g |

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Compliant<br><a href="#">EU RoHS Declaration</a>  |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |