



Main

Product or component type	Servo motor
Device short name	BSH
Maximum mechanical speed	6000 rpm
Continuous stall torque	5.5 N.m for LXM05AD14N4 at 380...480 V three phase 5.5 N.m for LXM05BD14N4 at 380...480 V three phase 5.5 N.m for LXM05CD14N4 at 380...480 V three phase
Peak stall torque	13.3 N.m for LXM05AD14N4 at 380...480 V three phase 13.3 N.m for LXM05BD14N4 at 380...480 V three phase 13.3 N.m for LXM05CD14N4 at 380...480 V three phase
Nominal output power	780 W for LXM05AD14N4 at 380...480 V three phase 780 W for LXM05BD14N4 at 380...480 V three phase 780 W for LXM05CD14N4 at 380...480 V three phase
Nominal torque	4.96 N.m for LXM05AD14N4 at 380...480 V three phase 4.96 N.m for LXM05BD14N4 at 380...480 V three phase 4.96 N.m for LXM05CD14N4 at 380...480 V three phase
Nominal speed	1500 rpm for LXM05AD14N4 at 380...480 V three phase 1500 rpm for LXM05BD14N4 at 380...480 V three phase 1500 rpm for LXM05CD14N4 at 380...480 V three phase
Product compatibility	LXM05AD14N4 at 380...480 V three phase LXM05BD14N4 at 380...480 V three phase LXM05CD14N4 at 380...480 V three phase
Shaft end	Untapped
IP degree of protection	IP50 (standard)
Speed feedback resolution	131072 points/turn x 4096 turns
Holding brake	With
Mounting support	International standard flange
Electrical connection	Straight connectors

Complementary

Range compatibility	Lexium 05
Supply voltage max	480 V

Network number of phases	Three phase
Continuous stall current	2.5 A
Maximum continuous power	2.51 W
Maximum current Irms	9 A for LXM05AD14N4 9 A for LXM05BD14N4 9 A for LXM05CD14N4
Maximum permanent current	9 A
Switching frequency	4 kHz
Second shaft	Without second shaft end
Shaft diameter	19 mm
Shaft length	40 mm
Feedback type	Multiturn SinCos Hiperface
Holding torque	9 N.m (holding brake)
Motor flange size	100 mm
Torque constant	2.32 N.m/A at 120 °C
Back emf constant	146 V/krpm at 120 °C
Number of motor poles	8
Rotor inertia	2.928 kg.cm ²
Stator resistance	8.6 Ohm at 20 °C
Stator inductance	45.7 mH at 20 °C
Stator electrical time constant	5.31 ms at 20 °C
Maximum radial force Fr	620 N at 4000 rpm 690 N at 3000 rpm 790 N at 2000 rpm 990 N at 1000 rpm
Maximum axial force Fa	0.2 x Fr
Brake pull-in power	18 W
Type of cooling	Natural convection
Length	235.5 mm
Centring collar diameter	95 mm
Centring collar depth	3.5 mm
Number of mounting holes	4
Mounting holes diameter	9 mm
Circle diameter of the mounting holes	115 mm
Product weight	6.3 kg

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0850 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------