

Product data sheet

Specifications



Shaver socket, AvatarOn, 115/240V, 20VA, White

E83T727V_WE_C5

Main

Range	AvatarOn
Product Or Component Type	Shaver socket
Installation Direction	Vertical
Input Voltage	240 V AC 50/60 Hz
Output Voltage	115 V AC 50/60 Hz 240 V AC 50/60 Hz
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: bracket Brass: terminals
Colour Tint	White

Complementary

Device Presentation	Complete product
Device Mounting	Surface
Cable Cross Section	1...2.5 mm²
Rated Operational Power In Va	20 VA
Connections - Terminals	Pillar terminals
Width	86 mm
Height	147 mm
Depth	50 mm

Environment

Ambient Air Temperature For Operation	-5...45 °C
Ambient Air Temperature For Storage	0...60 °C
Relative Humidity	0...95 %
Environmental Characteristic	UV resistant
Operating Altitude	2000 m
Ip Degree Of Protection	IP21
Standards	IEC 61558-2-5

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	6.3 cm
Package 1 Width	9.4 cm
Package 1 Length	15.3 cm
Package 1 Weight	150.0 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations