

Product data sheet

Specifications



Universal Shaver Unit, Vertical, Wine Gold

E84T727V_WG

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	ZENcelo
Product Or Component Type	Shaver socket
Installation Direction	Vertical
Input Voltage	240 V AC 50 Hz
Output Voltage	115 V AC 50 Hz 240 V AC 50 Hz
Material	Polycarbonate: base Polycarbonate: grid plate Polycarbonate: surround
Colour Tint	Wine gold

Complementary

Device Mounting	Flush Surface
Cable Cross Section	1...2.5 mm²
Rated Operational Power In Va	20 VA
Connections - Terminals	Pillar terminal without pressure plate
Electrical Insulation Class	Class B
Width	147 mm
Height	87 mm
Depth	49.3 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Operating Altitude	<= 2000 m
Ip Degree Of Protection	IP21
Standards	IEC 61558-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	6.3 cm
Package 1 Width	9.4 cm
Package 1 Length	15.5 cm
Package 1 Weight	600.0 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations