


Product data sheet

Specifications



AC servo motor BSH, Lexium 05, 5.5N.m, 1500rpm, keyed shaft, with brake, IP50

BSH1002M12F1A

ⓘ Discontinued

Main

Product Or Component Type	Servo motor
Device Short Name	BSH
Maximum Mechanical Speed	6000 rpm
Continuous Stall Torque	5.5 N.m for LXM05AD14N4, 380...480 V, three phase 5.5 N.m for LXM05BD14N4, 380...480 V, three phase 5.5 N.m for LXM05CD14N4, 380...480 V, three phase
Peak Stall Torque	13.3 N.m for LXM05AD14N4, 380...480 V, three phase 13.3 N.m for LXM05BD14N4, 380...480 V, three phase 13.3 N.m for LXM05CD14N4, 380...480 V, three phase
Nominal Output Power	780 W for LXM05AD14N4, 380...480 V, three phase 780 W for LXM05BD14N4, 380...480 V, three phase 780 W for LXM05CD14N4, 380...480 V, three phase
Nominal Torque	4.96 N.m for LXM05AD14N4, 380...480 V, three phase 4.96 N.m for LXM05BD14N4, 380...480 V, three phase 4.96 N.m for LXM05CD14N4, 380...480 V, three phase
Nominal Speed	1500 rpm for LXM05AD14N4, 380...480 V, three phase 1500 rpm for LXM05BD14N4, 380...480 V, three phase 1500 rpm for LXM05CD14N4, 380...480 V, three phase
Product Compatibility	LXM05AD14N4 at 380...480 V three phase LXM05BD14N4 at 380...480 V three phase LXM05CD14N4 at 380...480 V three phase
Shaft End	Keyed
Ip Degree Of Protection	IP50 standard
Speed Feedback Resolution	131072 points/turn x 4096 turns
Holding Brake	With
Mounting Support	International standard flange
Electrical Connection	Straight connectors

Complementary

Range Compatibility	Lexium 05
Supply Voltage Max	480 V
Network Number Of Phases	Three phase
Continuous Stall Current	2.5 A
Maximum Continuous Power	2.51 W
Maximum Current Irms	9 A for LXM05AD14N4 9 A for LXM05BD14N4 9 A for LXM05CD14N4

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Maximum Permanent Current	9 A
Switching Frequency	4 kHz
Second Shaft	Without second shaft end
Shaft Diameter	19 mm
Shaft Length	40 mm
Key Width	30 mm
Feedback Type	Multiturn SinCos Hiperface
Holding Torque	9 N.m holding brake
Motor Flange Size	100 mm
Torque Constant	2.32 N.m/A at 120 °C
Back Emf Constant	146 V/krpm at 120 °C
Number Of Motor Poles	8
Rotor Inertia	2.928 kg.cm²
Stator Resistance	8.6 Ohm at 20 °C
Stator Inductance	45.7 mH at 20 °C
Stator Electrical Time Constant	5.31 ms at 20 °C
Maximum Radial Force Fr	620 N at 4000 rpm 690 N at 3000 rpm 790 N at 2000 rpm 990 N at 1000 rpm
Maximum Axial Force Fa	0.2 x Fr
Brake Pull-In Power	18 W
Type Of Cooling	Natural convection
Length	235.5 mm
Centring Collar Diameter	95 mm
Centring Collar Depth	3.5 mm
Number Of Mounting Holes	4
Mounting Holes Diameter	9 mm
Circle Diameter Of The Mounting Holes	115 mm
Net Weight	6.3 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------