

Product data sheet

Specifications

Mureva FIX - installation tie - 273x9 mm - 100 pieces



ENN47962

Main

Product Range	Mureva FIX
Product Type	Installation tie
Colour Tint	Black
Quantity Per Set	100 pieces

Complementary

Minimum Tightening Diameter	26 mm
Maximum Tightening Diameter	62 mm
Resistance To Tearing	Resistance to tearing: 45 daN Ø 26 mm
Material	PA (polyamide) 12 Rislan®
Length	273 mm
Width	9 mm
Net Weight	0.004 kg

Environment

Maximum Humidity Absorption	0.9 %
Operating Temperature	-60...85 °C 100 °C during 1000 hours 120 °C maximum
Flame Retardance	HB conforming to UL 94
Standards	EN 50146
Environmental Characteristic	UV resistant

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.2 cm
Package 1 Width	0.9 cm
Package 1 Length	27.3 cm
Package 1 Weight	4 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations