

Product data sheet

Specifications



Asfora - rotary dimmer - 2-way - 600W - white - flow-pack

EPH6401121

⚠ Discontinued on: Dec 31, 2023

⚠ Discontinued

Main

| | |
|---------------------------|--|
| Range | Asfora |
| Product Or Component Type | Dimmer |
| Device Presentation | Complete product |
| Load Type | 12 V AC halogen lamp with standard mechanical transformer: 40...600 W 230 V AC halogen lamp: 40...600 W 230 V AC incandescent lamp: 40...600 W |
| Cover Frame Colour Tint | White |
| Type Of Packing | Flow-pack |

Complementary

| | |
|--------------------------------|---|
| Wiring Device Mounting | Flush |
| Switch Function | 1-pole 2-way |
| Dimmer Control | Rotary push type |
| Dimmer Application | Ohmic load Inductive load |
| [Ue] Rated Operational Voltage | 230 V AC 50 Hz |
| Colour Tint | White |
| Connections - Terminals | Pillar terminals |
| Number Of Cables | 3 cable(s) 2.5 mm ² |
| Cable Stiffness | Rigid Flexible |
| Wire Stripping Length | 7 mm |
| Material | ABS (acrylonitrile butadiene-styrene): central plate ABS (acrylonitrile butadiene-styrene): cover frame ABS (acrylonitrile butadiene-styrene): knob |
| Surface Finish | Glossy |
| Conductor Material | Copper |
| Fixing Mode | Claws53...78 mm |
| Height | 83 mm |
| Width | 83 mm |
| Depth | 50 mm |
| Projecting Depth | 21 mm |
| Net Weight | 0.111 kg |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

| | |
|-------------------------|---------------------------------------|
| Product Certifications | TSE VDE NEMKO FIMKO SEMKO |
| Ip Degree Of Protection | IP20 |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 8.5 cm |
| Package 1 Width | 8.4 cm |
| Package 1 Length | 6.2 cm |
| Package 1 Weight | 156 g |
| Unit Type Of Package 2 | S02 |
| Number Of Units In Package 2 | 24 |
| Package 2 Height | 15 cm |
| Package 2 Width | 30 cm |
| Package 2 Length | 40 cm |
| Package 2 Weight | 4.062 kg |
| Unit Type Of Package 3 | P12 |
| Number Of Units In Package 3 | 1536 |
| Package 3 Height | 135 cm |
| Package 3 Width | 80 cm |
| Package 3 Length | 120 cm |
| Package 3 Weight | 269.92 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

| | |
|--|---|
|  Mercury Free | |
|  Rohs Exemption Information | Yes |
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |