

Product data sheet

Specifications



AC servo motor BSH, Lexium 05, 5.5N.m, 4000rpm, untapped shaft, with brake, IP65

BSH1002T22F2A

Main

| | |
|---------------------------|--|
| Product Or Component Type | Servo motor |
| Device Short Name | BSH |
| Maximum Mechanical Speed | 6000 rpm |
| Continuous Stall Torque | 5.8 N.m for LXM32.D30M2 at 10 A, 230 V, single phase 5.5 N.m for LXM15LD28M3, 230 V, three phase 5.5 N.m for LXM05AD42M3X, 200...240 V, three phase 5.5 N.m for LXM05BD42M3X, 200...240 V, three phase 5.5 N.m for LXM05CD42M3X, 200...240 V, three phase |
| Peak Stall Torque | 16.4 N.m for LXM32.D30M2 at 10 A, 230 V, single phase 11.59 N.m for LXM15LD28M3, 230 V, three phase 16 N.m for LXM05AD42M3X, 200...240 V, three phase 16 N.m for LXM05BD42M3X, 200...240 V, three phase 16 N.m for LXM05CD42M3X, 200...240 V, three phase |
| Nominal Output Power | 1500 W for LXM32.D30M2 at 10 A, 230 V, single phase 1400 W for LXM05AD42M3X, 200...240 V, three phase 1400 W for LXM05BD42M3X, 200...240 V, three phase 1400 W for LXM05CD42M3X, 200...240 V, three phase 1700 W for LXM15LD28M3, 230 V, three phase |
| Nominal Torque | 3.7 N.m for LXM32.D30M2 at 10 A, 230 V, single phase 4 N.m for LXM15LD28M3, 230 V, three phase 4.4 N.m for LXM05AD42M3X, 200...240 V, three phase 4.4 N.m for LXM05BD42M3X, 200...240 V, three phase 4.4 N.m for LXM05CD42M3X, 200...240 V, three phase |
| Nominal Speed | 4000 rpm for LXM32.D30M2 at 10 A, 230 V, single phase 3000 rpm for LXM05AD42M3X, 200...240 V, three phase 3000 rpm for LXM05BD42M3X, 200...240 V, three phase 3000 rpm for LXM05CD42M3X, 200...240 V, three phase 4000 rpm for LXM15LD28M3, 230 V, three phase |
| Product Compatibility | LXM32.D30M2 at 230 V single phase LXM05AD42M3X at 200...240 V three phase LXM05BD42M3X at 200...240 V three phase LXM05CD42M3X at 200...240 V three phase LXM15LD28M3 at 230 V three phase |
| Shaft End | Untapped |
| Ip Degree Of Protection | IP65 standard IP67 with IP67 kit |
| Speed Feedback Resolution | 131072 points/turn x 4096 turns |
| Holding Brake | With |
| Mounting Support | International standard flange |
| Electrical Connection | Rotatable right-angled connectors |

Complementary

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---------------------------------------|---|
| Range Compatibility | Lexium 05 Lexium 32 Lexium 15 |
| Supply Voltage Max | 480 V |
| Network Number Of Phases | Three phase |
| Continuous Stall Current | 9.9 A |
| Maximum Continuous Power | 2.51 W |
| Maximum Current Irms | 31.2 A for LXM15LD28M3 35.4 A for LXM05AD42M3X 35.4 A for LXM05BD42M3X 35.4 A for LXM05CD42M3X 30 A for LXM32.D30M2 |
| Maximum Permanent Current | 35.4 A |
| Switching Frequency | 8 kHz |
| Second Shaft | Without second shaft end |
| Shaft Diameter | 19 mm |
| Shaft Length | 40 mm |
| Feedback Type | Multiturn SinCos Hiperface |
| Holding Torque | 9 N.m holding brake |
| Motor Flange Size | 100 mm |
| Number Of Motor Stacks | 2 |
| Torque Constant | 0.59 N.m/A at 120 °C |
| Back Emf Constant | 37 V/krpm at 120 °C |
| Number Of Motor Poles | 8 |
| Rotor Inertia | 2.928 kg.cm² |
| Stator Resistance | 0.56 Ohm at 20 °C |
| Stator Inductance | 3 mH at 20 °C |
| Stator Electrical Time Constant | 5.36 ms at 20 °C |
| Maximum Radial Force Fr | 620 N at 4000 rpm 690 N at 3000 rpm 790 N at 2000 rpm 990 N at 1000 rpm |
| Maximum Axial Force Fa | 0.2 x Fr |
| Brake Pull-In Power | 18 W |
| Type Of Cooling | Natural convection |
| Length | 235.5 mm |
| Centring Collar Diameter | 95 mm |
| Centring Collar Depth | 3.5 mm |
| Number Of Mounting Holes | 4 |
| Mounting Holes Diameter | 9 mm |
| Circle Diameter Of The Mounting Holes | 115 mm |
| Net Weight | 6.3 kg |

Packing Units

| | |
|------------------------|-----|
| Unit Type Of Package 1 | PCE |
|------------------------|-----|

| | |
|------------------------------|---------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 15.4 cm |
| Package 1 Width | 16.3 cm |
| Package 1 Length | 40.7 cm |
| Package 1 Weight | 6.45 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)


Certifications & Standards

| | |
|---------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

Dimensions Drawings

Servo Motors Dimensions

Example with Straight Connectors



- a: Power supply for servo motor brake
b: Power supply for servo motor encoder
(1) M4 screw
(2) Shaft end, keyed slot (optional)

Dimensions in mm

| Straight connectors | | Rotatable angled connectors | | c (without brake) | c (with brake) | c1 | c2 | h | h1 | Ø | Ø1 for screws |
|---------------------|------|-----------------------------|------|-------------------|----------------|----|----|------|----------------------------------|-------|---------------|
| b1 | b2 | b1 | b2 | | | | | | | | |
| 39.5 | 25.5 | 39.5 | 39.5 | 205 | 236 | 40 | 30 | 6 N9 | 3.5 ^{+0.1} ₀ | 19 k6 | M6 x 16 |

Dimensions in in.


| Straight connectors | | Rotatable angled connectors | | c (without brake) | c (with brake) | c1 | c2 | h | h1 | Ø | Ø1 for screws |
|---------------------|------|-----------------------------|------|-------------------|----------------|------|------|---------|-----------------------------------|---------|---------------|
| b1 | b2 | b1 | b2 | | | | | | | | |
| 1.55 | 1.00 | 1.55 | 1.55 | 8.07 | 9.29 | 1.57 | 1.18 | 0.24 N9 | 0.14 ^{+0.1} ₀ | 0.75 k6 | M6 x 0.63 |

Performance Curves

230 V Single-Phase Supply Voltage

Torque/Speed Curves

Servo motor with LXM32•D30M2 servo drive



- X Speed in rpm
- Y Torque in Nm
- 1 Peak torque
- 2 Continuous torque