

# Product data sheet

Specifications



## Asfora - 2-way rotary dimmer - RC, 20-315VA cream

EPH6600123

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

### Main

|                           |   |
|---------------------------|---|
| Range                     | Asfora  |
| Product Or Component Type | Dimmer  |
| Device Presentation       | Complete product  |
| Load Type                 | 230 V AC halogen lamp: 20...315 W<br>230 V AC incandescent lamp: 20...315 W<br>Low voltage halogen lamp with electronic transformer: 20...315 W |
| Colour Tint               | Cream   |
| Type Of Packing           | Box   |

### Complementary

|                                |   |
|--------------------------------|---|
| Device Mounting                | Flush   |
| Switch Function                | 1-pole 2-way  |
| Dimmer Control                 | Rotary push type  |
| Dimmer Application             | Capacitive load<br>Ohmic load   |
| Protection Type                | Short-circuit and overload protection with automatic reset  |
| [Ue] Rated Operational Voltage | 230 V AC 50 Hz  |
| Surface Finish                 | Glossy  |
| Material                       | ABS (acrylonitrile butadiene-styrene): central plate<br>ABS (acrylonitrile butadiene-styrene): cover frame<br>ABS (acrylonitrile butadiene-styrene): knob |
| Connections - Terminals        | Pillar terminals  |
| Number Of Cables               | 2 cable(s) 2.5 mm²  |
| Cable Stiffness                | Flexible<br>Rigid   |
| Wire Stripping Length          | 8 mm  |
| Conductor Material             | Copper  |
| Fixing Mode                    | Claws53...78 mm   |
| Height                         | 83 mm   |
| Width                          | 83 mm   |
| Depth                          | 49 mm   |
| Projecting Depth               | 20 mm   |
| Net Weight                     | 0.111 kg  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

|                         |  |
|-------------------------|--|
| Product Certifications  | FIMKO<br>TSE<br>SEMKO<br>GOST<br>NEMKO<br>UKR<br>VDE |
| Quality Labels          | CE   |
| Ip Degree Of Protection | IP20   |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type Of Package 1       | PCE       |
| Number Of Units In Package 1 | 1         |
| Package 1 Height             | 6.500 cm  |
| Package 1 Width              | 8.500 cm  |
| Package 1 Length             | 8.500 cm  |
| Package 1 Weight             | 154.000 g |
| Unit Type Of Package 2       | S02       |
| Number Of Units In Package 2 | 24        |
| Package 2 Height             | 15.000 cm |
| Package 2 Width              | 30.000 cm |
| Package 2 Length             | 40.000 cm |
| Package 2 Weight             | 3.875 kg  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

|  |   |
|--|---|
|  Mercury Free               |   |
|  Rohs Exemption Information | <a href="#">Yes</a>   |
| Reach Regulation   | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive  | Compliant with Exemptions   |
| China Rohs Regulation  | <a href="#">China RoHS declaration</a><br>Product out of China RoHS scope. Substance declaration for your information       |
| Weee   | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |