

Product data sheet

Specifications

Ultra - mini trunking - 16 x 16 mm - PVC - white - 2 m



ETK16916

Main

Range	Ultra
Product Or Component Type	Mini trunking
Device Application	Cable distribution
Colour Tint	White (RAL 9010)
Quantity Per Set	156 m
Main Colour Tint	White

Complementary

Trunking Material	Plastic
Compartment Partitioning	1 compartment
Trunking Dimension	16 x 16 mm
Fixing Mode	Pre-punched fixing hole 230 mm Power cable: screw-fixed Low voltage cable: adhesive tape
Material	PVC (polyvinyl chloride)
Length	2000 mm
Height	16 mm
Width	16 mm

Environment

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	-5...60 °C
Standards	EN 50085-1:2005 EN 50085-2-1:2006

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	1.5 cm
Package 1 Length	200.0 cm
Package 1 Weight	209.538 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	CAR
Number Of Units In Package 2	156
Package 2 Height	11.0 cm
Package 2 Width	22.5 cm
Package 2 Length	211.0 cm
Package 2 Weight	16.344 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations