

Product data sheet

Specifications



SE Easy UPS, 1000VA, Floor/Wall Mount, 230V, 6x IEC C13 outlets, AVR

BVS1000I

Overview

Lead Time	Usually in Stock
-----------	------------------

Main

Product Or Component Type	Uninterruptible power supply (UPS)
Battery Type	Lead-acid battery

Complementary

Input Voltage	230 V AC
Output Voltage	230 V AC
Transfer Time	6 ms typical : 10 ms maximum
Power Range	1000 VA 600 W
Electrical Connection	Input: 1 inlet IEC 320 C14 Output: 6 outlet IEC 320 C13
Local Signalling	Alarm, distinctive for low battery Alarm, continuous or intermittent tone for overload LED for battery status
Charging Time	8 h
Battery Voltage	12 V
Battery Capacity	9.0 Ah
Net Weight	5.7 kg
Height	92.5 mm
Width	160.5 mm
Depth	305 mm

Environment

Relative Humidity	0...90 %, non-condensing
Operating Altitude	0...6561 ft
Ambient Air Temperature For Operation	0...40 °C
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
Product Certifications	CE

Physical

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mounting Support	Wall
	Floor

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.200 cm
Package 1 Width	12.500 cm
Package 1 Length	30.500 cm
Package 1 Weight	5.702 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	4
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	23.458 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	32
Package 3 Height	90.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	199.664 kg
Scc14	10731304338380

Contractual warranty

Warranty	2 years
----------	---------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Compliant with Exemptions

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

[End of Life Information](#)