



### Main

Range	EVlink
Product name	EVlink parking
Product or component type	Enclosure
Device short name	EVP2
Range compatibility	EVlink parking EVF2 charging station EVlink parking EVW2 charging station
Poles description	3P + N for power circuit 1P + N for control circuit
Mounting mode	Wall-mounted Floor-standing
Offer type	Standard
[Us] rated supply voltage	230 V AC 50/60 Hz control circuit 380...415 V AC 50/60 Hz power circuit
Earthing system	IT TN TT
Socket number	2
Socket-outlet type	Right side : T2 / silver plated contacts Left side : T2 / silver plated contacts
Supply current	32 A for T2
Nominal output power	22 kW for T2

### Complementary

Control type	2 red push-button function: stop 2 green illuminated push-button function: start/unlock flap
Local signalling	2 green LED flashing on side device function: on charge 2 green LED on front device function: available 2 orange LED on front device function: reserved 2 red LED on front device function: not operational
Web server	Embedded
Ethernet service	Configuration via web server
Height	625 mm
Width	400 mm
Depth	206 mm

Product weight	20 kg
Colour	Grey RAL 7016

## Environment

IP degree of protection	IP54 off load conforming to IEC 61851-1 IP54 on load conforming to IEC 61851-1
IK degree of protection	IK10 charging station conforming to IEC 61851-22 IK10 socket-outlet conforming to IEC 61851-22
Ambient air temperature for operation	-25...50 °C conforming to IEC 61851-22
Ambient air temperature for storage	-40...80 °C
Operating altitude	0...2000 m conforming to IEC 61851-22
Relative humidity	0...95 %