



CA2KN315E72 has not been replaced. Please contact your customer care center for more information.

⚠ Discontinued

Main

Range	TeSys
Product name	TeSys CAK
Product or component type	Control relay
Device short name	CA2K
Contactor application	Control circuit
Utilisation category	DC-13 AC-15
Pole contact composition	3 NO + 1 NC
[Ue] rated operational voltage	≤ 690 V ≤ 400 Hz
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	48 V AC 50/60 Hz

Complementary

Coil technology	Built-in bidirectional peak limiting diode suppressor
[Ith] conventional free air thermal current	10 A at ≤ 50 °C
Irms rated making capacity	110 A conforming to IEC 60947
Associated fuse rating	10 A gG conforming to IEC 60947 10 A gG conforming to VDE 0660
[Ui] rated insulation voltage	600 V conforming to CSA C22.2 No 14 690 V conforming to BS 5424 690 V conforming to IEC 60947 750 V conforming to VDE 0110 group C
Mounting support	Rail Plate
Connections - terminals	Solder pins 1.5 x 0.9 mm
Control circuit voltage limits	0.2...0.75 Uc at ≤ 50 °C drop-out 0.8...1.15 Uc at ≤ 50 °C operational
Operating time	10...20 ms coil de-energisation and NO opening 5...15 ms coil energisation and NC opening 10...20 ms coil energisation and NO closing 15...25 ms coil de-energisation and NC closing
Mechanical durability	10 Mcycles
Operating rate	≤ 10000 cyc/h
Immunity to microbreaks	2 ms

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Inrush power in VA	30 VA at 20 °C
Hold-in power consumption in VA	4.5 VA at 20 °C
Heat dissipation	1.3 W
Minimum switching voltage	17 V
Minimum switching current	5 mA
Non overlap distance	0.5 mm
Insulation resistance	> 10 MOhm
Height	58 mm
Width	45 mm
Depth	57 mm
Product weight	0.21 kg

Environment

Standards	BS 5424 IEC 60947 VDE 0660 NF C 63-140
Product certifications	UL CSA
IP degree of protection	IP2x
Protective treatment	TC conforming to IEC 60068
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-50...80 °C
Operating altitude	2000 m without
Flame retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102
Mechanical robustness	Vibrations contactor closed 4 Gn, 5...300 Hz IEC 60068-2-6 Vibrations contactor open 2 Gn, 5...300 Hz IEC 60068-2-6 Shocks contactor open 10 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed 15 Gn for 11 ms IEC 60068-2-27

Contractual warranty

Warranty period	18 months
-----------------	-----------