

# Product data sheet

Specifications



## MV vacuum circuit breaker, EasyPact EXE, basic function, 12kV, 2500A, 25kA 3s, 275mm, IEC

EXE122525M1B

### Main

Master Range	Easy Series
Range Of Product	EasyPact
Product Name	EasyPact EXE
Switching Device	Circuit breaker
Breaking Technology	Vacuum
Product Or Component Type	Circuit breaker
Pole Type	Open
Number Of Poles	3
Network Type	AC
Type Of Installation	Indoor
Integration Type	Fixed
Variant	Basic function
Standards	IEC 62271-100:2012
Rated Voltage (Ur)	12 kV
Rated Short-Duration Power Frequency Withstand Voltage (Ud) / Common Value	28 kV
Rated Lightning Impulse Withstand Voltage (Up) / Common Value	75 kV
Rated Frequency (Fr)	50/60 Hz
Rated Continuous Current (Ir)	2500 A
Rated Short-Circuit Breaking Current (Isc)	25 kA
Rated Short-Circuit Making Current	62.5 kA 50 Hz 65 kA 60 Hz
Dc Time Constant (T)	45 ms
Dc Component	30 %
Rated Short-Time Withstand Current (Ik)	25 kA
Rated Duration Of Short-Circuit (Tk)	3 s
Rated Peak Withstand Current (Ip)	62.5 kA 50 Hz 65 kA 60 Hz
Rated First Pole-To-Clear Factor (Kpp)	1.5
Rated Out-Of-Phase Breaking Current (Id)	7.88 kA
Rated Line-Charging Breaking Current (Il)	10 A

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Rated Cable-Charging Breaking Current (Ic)	25 A
Rated Single Capacitor Bank-Breaking Current (Isb)	400 A
Rated Operating Sequence	O - 3 min - CO - 3 min - CO O - 0.3 s - CO - 3 min - CO O - 0.3 s - CO - 15 s - CO

## Complementary

Auxiliary Contact Composition	4 NO + 4 NC
Operating Time	< 50 ms opening time < 66 ms break-time < 71 ms closing time
Motor Charging Time	<= 7 s
Classification For Electrical Endurance	E2
Number Of Operations At Short-Circuit Breaking Current	50
Classification For The Connection To The Network	S1
Classification For Capacitive Currents	C2
Number Of Mechanical Operations	10000 operating cycles
Classification For Number Of Mechanical Operations	M2
Mass	70 kg
Height	527 mm
Width	724 mm
Depth	429 mm
Phase Distance	275 mm
Clearance In Air To Earth	140 mm
Upper Lower Connection Distance	270 mm

## Environment

Product Certifications	ASEFA
Ambient Air Temperature For Operation	-25...40 °C
Ambient Air Temperature For Storage	-25...55 °C
Humidity Conditions	Average relative humidity over 1 month <= 90 % Average relative humidity over 24 h <= 95 %
Operating Altitude	0...1000 m

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	73 cm
Package 1 Width	60 cm
Package 1 Length	80 cm
Package 1 Weight	105.0 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

Yes

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)