

Product data sheet

Specifications



Racking trolley, EasyPact EXE, motorization, 200 to 250V dc/ac, T2

EXERMCB20

Main

Range Of Product	EasyPact EXE
Device Short Name	motor
Product Or Component Type	Motor mechanism
[Us] Rated Supply Voltage	200...250 V DC 200...250 V AC
Device Application	Racking device motorization
Stroke Length	200 mm
Inrush Current	5 A
Maximum Operating Frequency	1 rack-in/rack-out per 3 minutes
Power Consumption In W	37 W
Input Current	0.2 A
Mounting Mode	Fixed
Accessory / Separate Part Type	Racking device

Complementary

Net Weight	1.8 kg
Height	52 mm
Width	52 mm
Depth	175 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12 cm
Package 1 Width	13 cm
Package 1 Length	35 cm
Package 1 Weight	2.25 kg
Unit Type Of Package 2	S02
Number Of Units In Package 2	2
Package 2 Height	15 cm
Package 2 Width	30 cm
Package 2 Length	40 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	5.14 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	16
Package 3 Height	75 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	49.62 kg