



### Main

Range of product	Easy9
Product or component type	Residual current circuit breaker (RCCB)
Device short name	Easy9 RCCB
Poles	2P
Neutral position	Left
[In] rated current	63 A
Network type	AC
Earth-leakage sensitivity	300 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type AC
Rated breaking and making capacity	500 A
Rated conditional short-circuit current	With Easy9 MCB : 4500 A 63 A

### Complementary

Device location in system	Outgoer
Network frequency	50 Hz
[Ue] rated operational voltage	230 V AC 50 Hz
Residual current tripping technology	Voltage dependent
[Ui] rated insulation voltage	440 V AC
[Uimp] rated impulse withstand voltage	4 kV
Contact position indicator	Yes
Control type	Toggle
Mounting mode	Clip-on
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top : YES
9 mm pitches	4

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Height	82 mm
Width	36 mm
Depth	72 mm
Colour	Grey RAL 7035
Mechanical durability	5000 cycles
Electrical durability	AC : 2000 cycles 230 V AC 50 Hz
Connections - terminals	Tunnel type terminal top or bottom 1...25 mm <sup>2</sup> rigid Tunnel type terminal top or bottom 1...16 mm <sup>2</sup> flexible
Tightening torque	2.5 N.m (top or bottom)
Market segment	Residential Small commercial

## Environment

Standards	IEC 61008-1
Product certifications	CE GOST-R EAC
IP degree of protection	IP20
Pollution degree	2 conforming to IEC 61008-1
Tropicalisation	2
Relative humidity	95 % ( 55 °C )
Ambient air temperature for operation	-25...60 °C
Ambient air temperature for storage	-40...85 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0844 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Available