

Product data sheet

Specifications



Acti9 - IC100k+ - 1C twilight switch - 1...99000 lux

CCT15251

⚠ Discontinued on: Dec 31, 2017

⚠ Discontinued

Main

Range Of Product	Acti9
Product Name	Acti9 IC
Product Or Component Type	Twilight switch
Device Short Name	IC100k
Provided Equipment	digital wall-mounted cell programming kit for PC digital switchboard cell
Load Type	230 V AC halogen lamp: 2600 W 230 V AC incandescent lamp: 2600 W parallel-corrected mercury and sodium vapour lamps: 800 VA 26 x 36 W non-corrected fluorescent tube with conventional ballast 20 x 58 W non-corrected fluorescent tube with conventional ballast 10 x 100 W non-corrected fluorescent tube with conventional ballast 26 x 36 W serial-corrected fluorescent tube with conventional ballast 20 x 58 W serial-corrected fluorescent tube with conventional ballast 10 x 100 W serial-corrected fluorescent tube with conventional ballast 26 x 36 W dual mounted fluorescent tube with conventional ballast 20 x 58 W dual mounted fluorescent tube with conventional ballast 10 x 100 W dual mounted fluorescent tube with conventional ballast 10 x 36 W parallel-corrected fluorescent tube with conventional ballast 6 x 58 W parallel-corrected fluorescent tube with conventional ballast 2 x 100 W parallel-corrected fluorescent tube with conventional ballast 18 x 11 W fluocompact lamp with electronic ballast 16 x 15 W fluocompact lamp with electronic ballast 16 x 20 W fluocompact lamp with electronic ballast 14 x 23 W fluocompact lamp with electronic ballast 22 x 7 W fluocompact lamp with electronic ballast motor: 2300 VA fluorescent tube with electronic ballast: 650 VA

Language	Danish Turkish Estonian Latvian Swedish German Italian English French Russian Dutch Finnish Lituanien Ukrainian
----------	--

Complementary

Device Application	Building
Number Of Channels	1
Power Consumption In Va	3 VA

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Ue] Rated Operational Voltage	230 V AC +10 % -15 % at 50/60 Hz
Maximum Switching Current	10 A - 250 V AC pf = 0.6 16 A - 250 V AC pf = 1
Electrical Insulation Class	Class II
Time Delay	< 60 s
9 Mm Pitches	4
Light Intensity Adjustment	1...99000 lux
Connections - Terminals	2 x 2.5 mm² screwless terminals
Height	90 mm
Width	36 mm
Depth	69 mm
Net Weight	183 g
Brightness Sensing Type	Digital wall-mounted cell
Control Type	By brightness detection
Market Segment	Residential Small commercial
Compatibility Code	IC100k

Environment

Ambient Air Temperature For Operation	-30...50 °C
Ip Degree Of Protection	IP20C
Standards	EN 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10 cm
Package 1 Width	10 cm
Package 1 Length	11 cm
Package 1 Weight	0.355 kg

Contractual warranty

Warranty	18 months
----------	-----------