



Main

Range of product	Acti 9
Product name	Acti 9 IHP
Device short name	IHP
Product or component type	Programmable digital time switch
Device application	Building
Battery type	Lithium
Number of channels	1
Language	English French German Italian Portuguese Spanish
Colour tint	White (RAL 9003)

Complementary

Product compatibility	Mechanical compatibility with electrical distribution comb busbars
Power consumption in VA	4 VA
Maximum switching current	10 A - 250 V AC pf = 0.6 16 A - 250 V AC pf = 1
[Ue] rated operational voltage	230 V[Sapce](+/- 10 %) AC 50/60 Hz
Cycle duration	24 hours + 7 days
Maximum number of switchings	56
Minimum interval duration	1 min
Accuracy	+/- 1 s/day 20 °C
Display type	Backlit LCD
Battery life	6 yr
Backup time	6 years time and program saving
Mounting support	DIN rail

9 mm pitches	5
Function available	Automatic winter/summer time changeover
Type of setting	Absence for holidays function
Connections - terminals	Screwless terminals
Width	45 mm
Height	85 mm
Depth	66 mm

Environment

IP degree of protection	IP20 B
Ambient air temperature for operation	-10...50 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1426 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available

Contractual warranty

Warranty period	18 months
-----------------	-----------