


Product data sheet

Specifications



circuit monitor CM4250 - data logging

CM4250MG

 **Discontinued on:** Dec 31, 2010

 **Discontinued**

Main

Range Of Product	PowerLogic
Device Short Name	CM4250
Product Or Component Type	Circuit monitor

Complementary

Power Quality Analysis	Programmability (logic and math functions) Disturbance direction detection Voltage sag and swell detection Setpoint learning Harmonic distortion Waveform capture Up to the 255th harmonic EN 50160 compliance checking
Device Application	Flicker
Type Of Measurement	Active power total Active power per phase Apparent power total Apparent power per phase Current Frequency Power factor total Power factor per phase Reactive power total Reactive power per phase Voltage
Supply Voltage	100...300 V DC 50/60 Hz 90...305 V AC
Network Frequency	50/60 Hz
Power Consumption In Va	50 VA
Sampling Rate	512 samples/cycle
Input Type	Current 0.005...10 A (impedance < 0.1 Ohm)25 x
Measurement Current	5 A
Measurement Voltage	0...1200 V, AC, with external VT, 0...1.5 Un 0...690 V, AC, direct, 0...1.5 Un
Measurement Accuracy	Current: 0.025 %, (full scale) Current: 0.04 %, (reading) Frequency: 0.01 Hz, 45...67 Hz Frequency: 0.1 Hz, 350...450 Hz Power: 0.025 %, (full scale) Power: 0.075 %, (reading) Voltage: 0.025 %, (full scale) Voltage: 0.04 %, (reading) Power factor: 0.002, from 0.5 leading to 0.5 lagging

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Accuracy Class	Class 0.2S energy conforming to ANSI C12.20 Class 0.2S energy conforming to IEC 62053-22
Number Of Outputs	1 pulse
Language	English German Spanish Italian Polish French
Communication Port Protocol	Modbus
Communication Port Support	RS232 RS485 RJ45: ETHERNET
Data Recording	Sequence of event recording Data logs Alarms Min/max of instantaneous values Event logs Time stamping Trending/forecasting
Memory Capacity	32 MB

Environment

Electromagnetic Compatibility	Conducted and radiated emissions: , A Electrostatic discharge immunity test: , III, conforming to IEC 61000-4-2 Electrical fast transient/burst immunity test: , III, conforming to IEC 61000-4-4 1.2/50 µs shock waves immunity test: , IV, conforming to IEC 61000-4-5 Susceptibility to electromagnetic fields: , III, conforming to IEC 61000-4-3
Overvoltage Category	IV
Ip Degree Of Protection	IP52 conforming to IEC 60529
Relative Humidity	5...95 % at 40 °C
Pollution Degree	2
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...85 °C
Standards	EN 61010 UL 508 CISPR 22
Width	235.5 mm
Depth	133.1 mm
Height	165.6 mm 216.3 mm
Net Weight	1.9 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Not compliant
