

Product data sheet

Specifications



Easy9 switch disconnecter - 4P - 125 A - 400 V

EZ9S16492

Main

Range	Easy9
Product Or Component Type	Switch
Device Short Name	Easy9 switch
Switch Application	Distribution
Poles	4P
Utilisation Category	AC-22A
Suitability For Isolation	Yes

Complementary

[Ie] Rated Operational Current	125 A at 400 V 50/60 Hz
[Ue] Rated Operational Voltage	400 V AC 50/60 Hz
[Icm] Rated Short-Circuit Making Capacity	1.875 kA
[Icw] Rated Short-Time Withstand Current	1.5 kA during 1 s
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	4 kV
Control Type	Toggle
Local Signalling	ON/OFF indication
Contact Position Indicator	Yes
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	8
Height	81 mm
Width	72 mm
Depth	66.5 mm
Colour	Grey
Mechanical Durability	7000 cycles
Electrical Durability	1000 cycles
Connections - Terminals	Tunnel type terminal (top or bottom) 1...50 mm² rigid Tunnel type terminal (top or bottom) 1...35 mm² flexible
Tightening Torque	3.5 N.m

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 60947-3
Product Certifications	CE
Ip Degree Of Protection	IP20 conforming to IEC 60529
Tropicalisation	2
Ambient Air Temperature For Operation	-5...55 °C
Ambient Air Temperature For Storage	-5...70 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.75 cm
Package 1 Width	7.21 cm
Package 1 Length	8.55 cm
Package 1 Weight	365.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	3
Package 2 Height	8.2 cm
Package 2 Width	8.8 cm
Package 2 Length	22.3 cm
Package 2 Weight	1.09 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	36
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	13.14 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations