



### Main

Range	Stago
Product or component type	Cover
Mounting location	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages

### Complementary

Operating angle	90 °
Direction change type	Vertical
Product destination	Rising piece KG281 for cable tray 35 mm 70 mm width Rising piece KG281 for cable tray 60 mm 70 mm width Rising piece KG281 for cable tray 85 mm 70 mm width Rising piece KG281 for cable tray 110 mm 70 mm width
Fixing mode	Screwless
Material with surface treatment	Steel pre-galvanized, RAL 9016
Colour tint	White (RAL 9016)
Corrosion class	C2
Length	219 mm
Net weight	0.261 kg / set of 1

### Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications