

# Product data sheet

Specifications



## Stago - ajustable corner piece - 110x100 - sheet steel - zinc+ - T=1 mm

CSU81521004

⚠ Discontinued on: Sep 25, 2020

⚠ End-of-service on: Dec 18, 2020

⚠ Discontinued

### Main

Range Of Product	Stago
Range	Stago
Product Or Component Type	Corner piece
Device Application	Cable management

### Complementary

Direction Change Type	Horizontal
Adjustment	Adjustable
Product Destination	Cable tray KB184 Zinc+ H= 110 mm W= 100 mm
Mounting Mode	Push-in
Fixing Mode	By screw
Shape	Bended
Material With Surface Treatment	Stainless steel zinc+
Thickness	1 mm

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.1 cm
Package 1 Width	32.7 cm
Package 1 Length	41 cm
Package 1 Weight	605 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations