

# Product data sheet

Specifications



## Stago - external riser fixed - 60x600 mm - sheet steel - zinc+ - T=1.5 mm

CSU86226006

 **Discontinued on:** Dec 11, 2019

 **Discontinued**

### Main

Range Of Product	Stago
Range	Stago
Product Or Component Type	Riser
Device Application	Cable management

### Complementary

Operating Angle	90 °
Direction Change Type	Vertical
Adjustment	Fixed
Product Destination	Cable tray KB184 Zinc+ H= 60 mm W= 600 mm
Shape	Bended
Fixing Mode	By screw
Material	Sheet steel zinc+
Thickness	1.5 mm

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25.7 cm
Package 1 Width	59.8 cm
Package 1 Length	25.7 cm
Package 1 Weight	2.206 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations