

Product data sheet

Specifications



TeSys LE - enclosure for DOL starter - with selector switch and pushbutton

DE1DS1A09

⚠ Discontinued on: Sep 18, 2020

⚠ Discontinued

Main

Range Of Product	TeSys
Range	TeSys
Device Short Name	DE1D
Product Or Component Type	Enclosure
Material	Polycarbonate
Device Composition	Contactors ordered separately Thermal overload relay ordered separately
Product Compatibility	LE1D12 LE1D09
Control Type	Push-button reset blue R Selector switch 3 positions automatic start/stop/manual start I-O-II

Complementary

Cable Entry Number	2 ISO20 top 2 ISO20 bottom 2 Pg 13 bottom 2 Pg 16 bottom
Height	166 mm
Width	88 mm
Depth	165 mm
Net Weight	0.3 kg

Environment

Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 60529
Ambient Air Temperature For Operation	-5...40 °C
Environmental Characteristic	Standard environment

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15 cm
Package 1 Width	15 cm
Package 1 Length	20.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	561 g
------------------	-------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive Compliant
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)