

# Product data sheet

Specifications



Cable end, Linergy TR cable ends,  
Single conductor, white, 0.5mm<sup>2</sup>,  
medium size, markable, insulated,  
10 sets of 100

DZ5CA005D

## Main

Range Of Product	Linergy
Product Or Component Type	Cable end
Cable End Size	Medium
Standards	DIN 46228-4
Type Of Packing	String of bags
Quantity Per Set	10 sets of 100
Cable Cross Section	0.5 mm <sup>2</sup>

## Complementary

Cable End Type	Single conductor
Additional Information	With integrated marker tag holder
Colour	White
Bezel Material	Halogen-free plastic
Tube Material	Copper conforming to ISO 1337
Number Of Cables	1
Awg Gauge	AWG 22
Bezel Size	Ø 3.1 mm
Tube Diameter	1.3 mm
Length	14 mm
Tube Length	8 mm
Cad Overall Depth	32 mm
Net Weight	0.16 kg

## Environment

Product Certifications	UL
Ambient Air Temperature For Operation	-20...105 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.400 cm
Package 1 Width	0.400 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	1.400 cm
Package 1 Weight	0.100 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	1000
Package 2 Height	4.000 cm
Package 2 Width	10.000 cm
Package 2 Length	21.000 cm
Package 2 Weight	139.000 g
Unit Type Of Package 3	S02
Number Of Units In Package 3	20000
Package 3 Height	15.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	3.137 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Pvc Free

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations