

Product data sheet

Specifications



16A INTERMEDIATE SWITCH, HORIZONTAL, GREY SILVER

E3031HIA_EBGS_G19

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range	Neo
Wiring Device Mounting	Surface Flush
Switch Function	Intermediate
Switch Application	Switch
Load Type	Inductive Fluorescent lamp Resistive
Bulb Type	LED (blue)
Colour Tint	Grey silver

Complementary

Rated Current	16 AX at 250 V AC 50 Hz 20 A at 250 V AC 50 Hz
Number Of Gangs	1 gang horizontal
Material	Brass: metal parts Polycarbonate: plastic part
Clamping Connection Capacity	3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s)
Connections - Terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding Depth	23.5 mm
Depth	36 mm

Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use
Standards	SS 227 IEC 60669-1 MS 616

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.7 cm
Package 1 Width	8.7 cm
Package 1 Length	3.6 cm
Package 1 Weight	0.001 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	End of Life Information