

# Product data sheet

Specifications



gearbox straight teeth GBX, Lexium,  
120mm, reduction 10:1 , 7arc.min,  
95N.m

GBX120010K

## Main

Range Compatibility	Lexium 32 Lexium 62 Lexium 28 Lexium 62 ILM Lexium 52
Gear Box Type	Straight teeth
Product Or Component Type	Planetary gearbox
Device Short Name	GBX
Product Compatibility	BMH (100 mm, 3 motor stacks) BSH (100 mm, 1 motor stacks) BSH (100 mm, 3 motor stacks) BCH2 (100 mm, 1 motor stacks) BCH2 (130 mm, 1 motor stacks) SH3 MH3 ILM
Gearbox External Diameter	120 mm
Reduction Ratio	10:1

## Complementary

Maximum Torsional Backlash	7 arc.min
Torsional Rigidity	12 N.m/arcmin
Housing Colour	Black
Housing Material	Black anodized aluminium
Shaft Material	C 45
Additional Information	Lubricated for life
Service Life In Hours	30000 h at 100 rpm at 30 °C
Mounting Position	Any position
Efficiency	96 %
Maximum Radial Force Fr	1500 N at 100 rpm, force applied at mid-distance from output shaft during 30000 hour at 30 °C
Maximum Axial Force Fa	2100 N at 100 rpm, during 30000 hour at 30°C
Moment Of Inertia	1.3 kg.cm <sup>2</sup>
Continuous Output Torque	95 N.m at 100 rpm at 30 °C
Maximum Output Torque	152 N.m at 100 rpm at 30 °C
Net Weight	6 kg
Input Diameter	24.0 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

Noise Level	65 dB at 1 m, no-load
Ip Degree Of Protection	Shaft output: IP54
Ambient Temperature For Operation	-25...90 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19.0 cm
Package 1 Width	13.0 cm
Package 1 Length	13.0 cm
Package 1 Weight	5.484 kg
Unit Type Of Package 2	S02
Number Of Units In Package 2	2
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	11.423 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)


[Guide to assess a product's sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation		<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
California Proposition 65		WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>

Dimensions Drawings

Dimensions with Servo Motor Adaptation Kit



- (1) GBK adaptation kit
- (2) GBK adaptation kit related dimensions a1, c, Ø6, Ø7, Ø8 depend on the gearbox and servo motor combination
- Ø8 shaft end adaptor in case motor shaft diameter is smaller than gearbox input coupling diameter

Values in mm

a2	a3	a4	a5	h	g	Ø1	Ø2	Ø3	Ø4	Ø5
99.5	55	50	5	28	8	115	80 h7	25 h7	M10 x 16	100

Values in in.

a2	a3	a4	a5	h	g	Ø1	Ø2	Ø3	Ø4	Ø5
3.92	2.17	1.97	0.19	1.10	0.31	4.53	3.15 h7	0.98 h7	M10 x 0.63	3.94