

Product data sheet

Specifications



16AX 250V 1 Gang Intermediate Switch with Fluorescent Locator, White

E8231MF_WE

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	Pieno
Product Or Component Type	Switch
Switch Application	Switch
Load Type	Fluorescent Resistive
Cover Frame Colour Tint	White

Complementary

Device Mounting	Surface Flush
Wiring Device Mounting	Flush Surface
Switch Function	Intermediate
Rated Current	16 AX at 250 V AC 50 Hz
Local Signalling	Fluorescent (white)
Number Of Gangs	1 gang
Material	Polycarbonate: surround Polycarbonate: grid plate
Connections - Terminals	Pillar terminals
Clamping Connection Capacity	2 x 1.5 mm ² for stranded cable(s) 2 x 2.5 mm ² for solid cable(s)
Embedding Depth	19.6 mm
Width	87 mm
Height	87 mm
Depth	19.6 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Standards	BS EN 60669-1 SS 227-1 IEC 60669-1 GB 16915.1 MS IEC 60669-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.2 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	108 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	6 cm
Package 2 Weight	617 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	60
Package 3 Height	32.5 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	6474.6 g

Contractual warranty

Warranty	18 months
----------	-----------