

Product data sheet

Specifications



Switch, AvatarOn, brass pillar, white

E8331ETPE3_WE

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	AvatarOn
Product Or Component Type	Switch
Device Application	Control
Device Presentation	Complete product
Load Type	Incandescent lamp - 200 W - 220...240 V AC LED lamp - 60 W - 220...240 V AC High voltage halogen lamp - 200 W - 220...240 V AC Low voltage halogen lamp with ferromagnetic transformer - 200 VA Low voltage lamps with electronic transformer - 200 VA Fluorescent lamp with conventional ballast - 100 VA - 220...240 V AC Fluorescent lamp with electronic ballast - 100 VA - 220...240 V AC Compact fluorescent lamp - 60 W - 220...240 V AC
Colour Tint	White (RAL 9003)
Type Of Packing	Gift box

Complementary

[Ue] Rated Operational Voltage	220...240 V AC 50/60 Hz
Supply Voltage Limits	198...264 V AC
Current Consumption	0.846 mA at 220...240 V AC
Protection Type	Overvoltage protection Overload protection
Actuator	Push-button
Fixing Mode	By screws
Fixing Center	60.3 mm
Surface Finish	Glossy
Time Delay	60 s, tolerance +/- 10 s
Mechanical Durability	20000 cycles
Number Of Terminals	3
Screwdriver Shape	Phillips combined
Clamping Connection Capacity	2 x 2.5 mm² for rigid cable(s) 2 x 2.5 mm² for stranded cable(s) 2 x 2.5 mm² for flexible cable(s)
Wire Stripping Length	12...15 mm
Connections - Terminals	Brass pillar
Local Signalling	LED (red) for on/off indication

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Material	Polycarbonate: plastic part Zinc plated steel: terminal screw
Device Mounting	Flush
Height	86 mm
Width	86 mm
Depth	33.18 mm

Environment

Ip Degree Of Protection	IP20
Ambient Air Temperature For Operation	0...40 °C
Ambient Air Temperature For Storage	0...60 °C
Relative Humidity	10...95 %, non-condensing (storage) 10...95 %, non-condensing (operating)
Operating Altitude	0...2000 m
Environmental Characteristic	Dust resistant Oil resistant Salt mist UV resistant
Standards	IEC 60669-2-1:ed. 4.1, 2009 CE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.63 cm
Package 1 Width	8.8 cm
Package 1 Length	8.8 cm
Package 1 Weight	97 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	19 cm
Package 2 Length	19.5 cm
Package 2 Weight	876 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	48
Package 3 Height	21 cm
Package 3 Width	30 cm
Package 3 Length	39.5 cm
Package 3 Weight	5756 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information