



Main

Range	AvatarOn
Product or component type	Dimmer + switch
Device presentation	Complete product
Provided equipment	Screws
Dimmer application	Capacitive load Inductive load Ohmic load
Dimmer control	225° rotary setting Dimming ON/OFF integrated
Load type	Incandescent lamps - 50...250 W - 220...240 V AC High voltage halogen lamp - 50...250 W - 220...240 V AC Electronic transformer - 50...250 VA Dimmable LED - 3...100 W
Colour tint	White
Type of packing	Carton
Quantity per set	Set of 8

Complementary

[Ue] rated operational voltage	220...240 V AC 50/60 Hz
Protection type	Thermal fuse Surge arrester
Number of modules	1 module
Actuator	Knob
Fixing mode	By screws
Clamping connection capacity	<= 2 x 2.5 mm ² for flexible cable(s) <= 2 x 2.5 mm ² for rigid cable(s)
Wire stripping length	12 mm
Material	Polycarbonate: plastic part Brass: terminals Steel coated with zinc chromate: terminal screw
Device mounting	Flush
Embedding depth	35 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

IP degree of protection	IP20
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	0...60 °C
Relative humidity	10...95 %
Environmental characteristic	Oil and vapour resistant
Standards	IEC 60669-2-1 CE
Directives	2011/65/EU - RoHS directive

Offer Sustainability

EU RoHS Directive	Will be compliant – Date to be confirmed
-------------------	--