

Product data sheet

Specifications



Mureva TUBE - elbow - grey - Ø25 mm

ENN42325

Main

Range Of Product	Mureva
Product Or Component Type	Elbow
Colour	Grey (RAL 7035)
Quantity Per Package	25 pieces

Complementary

Accessory / Separate Part Category	Installation accessory
Condition Of Use	Indoor/outdoor
Material	PVC (polyvinyl chloride)
Crush Resistance	750 N/m
Nominal Cross Section	119 mm²
Internal Diameter	21.3 mm
External Diameter	25 mm
Net Weight	0.028 kg

Environment

Operating Temperature	-5...60 °C
Quality Labels	NF
Standards	EN 61386-21 : 2004 EN 50086-2-1
Environmental Characteristic	Non-flame propagating
Ip-Class	IP40
Ik-Class	IK07

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	2.5 cm
Package 1 Length	5 cm
Package 1 Weight	28 g

Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations