



GC2511M6 has not been replaced. Please contact your customer care center for more information.

ⓘ Discontinued

## Main

Range	TeSys
Product name	TeSys GC
Product or component type	Modular contactor
Device short name	GC25
Contacteur application	Heating Motor control Lighting

## Complementary

Utilisation category	AC-7A AC-7B
Poles description	2P
Power pole contact composition	1 NO + 1 NC
[Ue] rated operational voltage	<= 250 V AC
[Ie] rated operational current	25 A AC-7A 8.5 A AC-7B
Operating position	30°/vertical
Control circuit type	AC 60 Hz
[Uc] control circuit voltage	220...240 V AC 60 Hz
[Uimp] rated impulse withstand voltage	4 kV
[Ith] conventional free air thermal current	25 A at <= 50 °C for power circuit
Irms rated making capacity	68 A at 400 V AC for power circuit conforming to IEC 61095
Rated breaking capacity	68 A at 400 V for power circuit conforming to IEC 61095
[Icw] rated short-time withstand current	200 A <= 40 °C 10 s power circuit 62 A <= 40 °C 30 s power circuit
Associated fuse rating	25 A gL at <= 440 V for power circuit
Average impedance	2.5 mOhm at 50 Hz - Ith 25 A for power circuit
[Ui] rated insulation voltage	500 V conforming to IEC 61095 500 V conforming to VDE 0110
Electrical durability	AC-7A : 100000 cycles AC-7B : 100000 cycles
Power dissipation per pole	1.6 W
Control type	Remote control

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mounting mode	Clip-on
Mounting support	DIN rail
Standards	IEC 60947-5 IEC 61095
Connections - terminals	Control circuit : screw clamp terminals 1 cable(s) 2.5 mm <sup>2</sup> - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 2 cable(s) 2.5 mm <sup>2</sup> - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 1 cable(s) 2.5 mm <sup>2</sup> - cable stiffness: flexible - with cable end Control circuit : screw clamp terminals 2 cable(s) 1.5 mm <sup>2</sup> - cable stiffness: flexible - with cable end Control circuit : screw clamp terminals 1 cable(s) 1.5 mm <sup>2</sup> - cable stiffness: solid - without cable end Control circuit : screw clamp terminals 2 cable(s) 1.5 mm <sup>2</sup> - cable stiffness: solid - without cable end Power circuit : screw clamp terminals 1 cable(s) 6 mm <sup>2</sup> - cable stiffness: flexible - without cable end Power circuit : screw clamp terminals 2 cable(s) 4 mm <sup>2</sup> - cable stiffness: flexible - without cable end Power circuit : screw clamp terminals 1 cable(s) 6 mm <sup>2</sup> - cable stiffness: flexible - with cable end Power circuit : screw clamp terminals 2 cable(s) 1.5 mm <sup>2</sup> - cable stiffness: flexible - with cable end Power circuit : screw clamp terminals 1 cable(s) 6 mm <sup>2</sup> - cable stiffness: solid - without cable end Power circuit : screw clamp terminals 2 cable(s) 4 mm <sup>2</sup> - cable stiffness: solid - without cable end
Tightening torque	Control circuit : 0.8 N.m - on screw clamp terminals Power circuit : 0.8 N.m - on screw clamp terminals
Operating time	10...25 ms opening 10...30 ms closing
Mechanical durability	1000000 cycles
Operating rate	300 cyc/h at <= 50 °C
Control circuit voltage limits	0.2...0.75 Uc at <= 50 °C drop-out 50 Hz 0.85...1.1 Uc at <= 50 °C operational 50 Hz
Hold-in power consumption in VA	3.8 VA at 20 °C 50 Hz
Heat dissipation	1.3 W at 50/60 Hz

## Environment

IP degree of protection	IP20 conforming to VDE 0106 IP40 in enclosure conforming to VDE 0106
Protective treatment	TC
Ambient air temperature for operation	-5...50 °C
Ambient air temperature for storage	-40...70 °C
Operating altitude	<= 3000 m
Mechanical robustness	Vibrations contactor open 2 Gn, 5...300 Hz Shocks contactor open 10 Gn for 11 ms Shocks contactor closed 15 Gn for 11 ms Vibrations contactor closed 3 Gn, 5...300 Hz
Total number of 18 mm modules	1
Height	81 mm
Width	17.5 mm
Depth	62.5 mm
Product weight	0.11 kg
Quantity per set	Set of 12
Colour	White

## Contractual warranty

Warranty period	18 months
-----------------	-----------