



Main

Range	Asfora
Product or component type	Switch
Device presentation	Without frame
Load type	Load for energy saving lamps with ballast : 100 W
Colour tint	Aluminium
Type of packing	Flow-pack

Complementary

Switch function	Double 2-way
Number of rocker	2
Device mounting	Flush
Power range	2300 W
Rated current	10 AX 250 V AC
Marking	Without marking
Connections - terminals	Lift terminals
Number of cables	2 x 2.5 mm ²
Cable stiffness	Flexible Rigid Solid stranded
Wire stripping length	13 mm
Material	ABS (acrylonitrile butadiene-styrene)
Surface finish	Painted
Conductor material	Copper
Fixing mode	Screws or claws 51...70 mm
Height	71 mm
Width	71 mm
Depth	43 mm
Projecting depth	15 mm
Product weight	0.07 kg
Quantity per set	Set of 1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 60669-1
Product certifications	VDE
Quality labels	CE
IP degree of protection	IP20