

Product data sheet

Specifications



Asfora - double USB charger 2.1 A - anthracite

EPH2700271

Main

Range	Asfora
Product Or Component Type	USB charger
Device Presentation	Mechanism with fixing frame
Device Mounting	Flush

Complementary

Device Application	Charger
Fixing Mode	By screws By claws
Number Output Current	2.1 A
Integrated Connection Type	2 USB 2.0 port 5 V DC, maximum load current: 2.1 A
[Ue] Rated Operational Voltage	100...240 V AC +/- 10 % at 50/60 Hz
Power Consumption In W	0.1 W
Nominal Output Power	10.5 W
Input Power	12 W
Surface Treatment	Untreated
Material	ABS (acrylonitrile butadiene-styrene): centre plate PC (polycarbonate) GF10 FR: casing PC (polycarbonate) GF10 FR: internal cover
Type Of Packing	Flow-pack
Clamping Connection Capacity	2 x 0.75...2 x 2.5 mm² for rigid cable(s) 2 x 0.75...2 x 2.5 mm² for flexible cable(s) 2 x 0.75...2 x 2.5 mm² for stranded cable(s)
Service Life In Hours	30000 h 10.5 W
Protection Type	Short-circuit protection
Number Of Terminals	2 screw terminals
Wire Stripping Length	8 mm
Product Compatibility	Mobile/tablet Mac iOS Mobile/tablet Android Mobile/tablet Windows
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP20
Height	83 mm
Width	83 mm
Depth	42 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Embedding Depth	30.8 mm
-----------------	---------

Environment

Standards	EN 60950-1 EN 62684 ETSI EN 301 489-4
Directives	2006/95/EC - low voltage directive 2004/108/EC - electromagnetic compatibility
Ambient Air Temperature For Operation	0...40 °C
Ambient Air Temperature For Storage	-5...50 °C
Product Certifications	EAC
Electrical Insulation Class	Class II

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	6.3 cm
Package 1 Length	6.3 cm
Package 1 Weight	121.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	24
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	2.904 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations