


Product data sheet

Specifications



13A Twin 3 Pin Switched Socket Outlet, White

ET3025_WW

Main

Range	Neo C-Metro
Product Or Component Type	Socket-outlet
Switch Function	1-pole
Outlet Poles Configuration	3P with shutters
Outlet Standard	BS 1363 SS 145 MS 589
Colour Tint	White

Complementary

Wiring Device Mounting	Surface Flush
Rated Current	13 A at 250 V AC 50/60 Hz
Material	Brass: contact Copper with silver onlay: bridge Nylon: shutter Polycarbonate: grid plate Polycarbonate: surround Steel with brass plating: screws Steel with brass plating: terminals
Load Type	Resistive
Connections - Terminals	Pillar terminals
Width	147 mm
Height	87 mm
Depth	18 mm

Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use
Standards	BS 1363 SS 145 MS 589

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	2.2 cm
Package 1 Width	8.6 cm
Package 1 Length	14.6 cm
Package 1 Weight	300.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	End of Life Information