


# Product data sheet

Specifications



## Easergy ETB 14 Single Test Block, Vertical Mounting, 14 circuits

ETB14-V

⚠ Discontinued on: Jul 20, 2023

⚠ Discontinued

### Main

Range Of Product	Easergy TestBlock
Device Short Name	ETB14-V
Device Composition	14 cassettes
Product Or Component Type	Test block
Operating Position	Vertical

### Complementary

[Ue] Rated Operational Voltage	300 V AC/DC conforming to IEC 60255
[Ie] Rated Operational Current	20 A
Inrush Current	400 A during 1 s

### Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529 (without protective cover) IP50 conforming to IEC 60529 (with protective cover)
Dielectric Strength	2 kV conforming to IEC 60255-5 (between input and output) 2 kV conforming to IEC 60255-5 (between open contacts) 5 kV at 1 min conforming to IEC 60255-5 (between earth and power terminals)
Environmental Characteristic	Exposure to cold: conforming to IEC 60068-2-1 Exposure to dry heat: conforming to IEC 60068-2-2 Continuous exposure to damp heat: 56 d 93 % 40 °C conforming to IEC 60068-2-78
Mechanical Robustness	Vibrations class II conforming to IEC 60255-21-1 Vibrations class II conforming to IEC 60255-21-2
Ambient Air Temperature For Operation	-25...55 °C
Ambient Air Temperature For Storage	-25...70 °C
Product Certifications	UL CE
Height	177.8 mm
Width	51.6 mm
Depth	203 mm
Net Weight	1.49 kg

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	5.16 cm
Package 1 Width	17.78 cm
Package 1 Length	20.3 cm
Package 1 Weight	1.85 kg