

Product data sheet

Specifications

Ultra - mini trunking - 16 x 16 mm - PVC - white - 2 m



ETK16316

Main

Range	Ultra
Product Or Component Type	Mini trunking
Device Application	Cable distribution
Quantity Per Set	132 m
Market Segment	Small commercial Residential

Complementary

Trunking Material	Plastic
Compartment Partitioning	1 compartment
Trunking Dimension	16 x 16 mm
Fixing Mode	Pre-punched fixing hole 230 mm Power cable: screw-fixed
Material	PVC (polyvinyl chloride)
Length	2000 mm
Height	16 mm
Width	16 mm

Environment

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	-5...60 °C
Standards	EN 50085-1:2005 EN 50085-2-1:2006

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.0 cm
Package 1 Width	2.0 cm
Package 1 Length	200.0 cm
Package 1 Weight	496.834 g
Unit Type Of Package 2	BB1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	132
Package 2 Height	11.0 cm
Package 2 Width	19.0 cm
Package 2 Length	200.0 cm
Package 2 Weight	32.791 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations