



Main

Range	TeSys
Product name	TeSys GC
Product or component type	Modular contactor
Device short name	GC63
Contacteur application	Heating Lighting Motor control

Complementary

Utilisation category	AC-7B AC-7A
Poles description	3P
Power pole contact composition	3 NO
[Ue] rated operational voltage	$\leq 250$ V AC
[Ie] rated operational current	25 A AC-7B 63 A AC-7A
Operating position	30°/Vertical
Control circuit type	AC 50 Hz
[Uc] control circuit voltage	110 V AC 50 Hz
[Uimp] rated impulse withstand voltage	4 kV
[Ith] conventional free air thermal current	63 A at $\leq 50$ °C for power circuit
Irms rated making capacity	200 A at 400 V AC for power circuit conforming to IEC 61095
Rated breaking capacity	200 A at 400 V for power circuit conforming to IEC 61095
[Icw] rated short-time withstand current	504 A $\leq 40$ °C 10 s power circuit 157 A $\leq 40$ °C 30 s power circuit
Associated fuse rating	63 A gL at $\leq 440$ V for power circuit
Average impedance	2 mOhm at 50 Hz - Ith 63 A for power circuit
[Ui] rated insulation voltage	500 V conforming to IEC 61095

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

500 V conforming to VDE 0110

Electrical durability	AC-7A : 100000 cycles AC-7B : 100000 cycles
Power dissipation per pole	8 W
Control type	Remote control
Mounting mode	Clip-on
Mounting support	DIN rail
Standards	IEC 61095 IEC 60947-5
Connections - terminals	Control circuit : screw clamp terminals 1 cable(s) 2.5 mm <sup>2</sup> - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 2 cable(s) 2.5 mm <sup>2</sup> - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 1 cable(s) 2.5 mm <sup>2</sup> - cable stiffness: flexible - with cable end Control circuit : screw clamp terminals 2 cable(s) 1.5 mm <sup>2</sup> - cable stiffness: flexible - with cable end Control circuit : screw clamp terminals 1 cable(s) 1.5 mm <sup>2</sup> - cable stiffness: solid - without cable end Control circuit : screw clamp terminals 2 cable(s) 1.5 mm <sup>2</sup> - cable stiffness: solid - without cable end Power circuit : screw clamp terminals 1 cable(s) 25 mm <sup>2</sup> - cable stiffness: flexible - without cable end Power circuit : screw clamp terminals 2 cable(s) 16 mm <sup>2</sup> - cable stiffness: flexible - without cable end Power circuit : screw clamp terminals 1 cable(s) 16 mm <sup>2</sup> - cable stiffness: flexible - with cable end Power circuit : screw clamp terminals 2 cable(s) 4 mm <sup>2</sup> - cable stiffness: flexible - with cable end Power circuit : screw clamp terminals 1 cable(s) 25 mm <sup>2</sup> - cable stiffness: solid - without cable end Power circuit : screw clamp terminals 2 cable(s) 6 mm <sup>2</sup> - cable stiffness: solid - without cable end
Tightening torque	Control circuit : 0.8 N.m - on screw clamp terminals Power circuit : 2 N.m - on screw clamp terminals
Operating time	10...25 ms opening 10...30 ms closing
Mechanical durability	1000000 cycles
Operating rate	300 cyc/h at ≤ 50 °C
Control circuit voltage limits	0.2...0.75 U <sub>c</sub> at ≤ 50 °C drop-out 50 Hz 0.85...1.1 U <sub>c</sub> at ≤ 50 °C operational 50 Hz
Hold-in power consumption in VA	6.5 VA at 20 °C 50 Hz
Heat dissipation	2.1 W at 50/60 Hz

## Environment

IP degree of protection	IP20 conforming to VDE 0106 IP40 in enclosure conforming to VDE 0106
Protective treatment	TC
Ambient air temperature for operation	-5...50 °C
Ambient air temperature for storage	-40...70 °C
Operating altitude	≤ 3000 m
Mechanical robustness	Vibrations contactor open 2 Gn, 5...300 Hz Shocks contactor open 10 Gn for 11 ms Shocks contactor closed 15 Gn for 11 ms Vibrations contactor closed 3 Gn, 5...300 Hz
Total number of 18 mm modules	3
Height	85 mm
Width	54 mm
Depth	62.5 mm
Product weight	0.39 kg
Quantity per set	Set of 4
Colour	White

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0610 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

---

Product environmental profile	Available <a href="#">Product Environmental Profile</a>
-------------------------------	--

---

Product end of life instructions	Need no specific recycling operations
----------------------------------	---------------------------------------

---

### Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---