



Main

Range	EVlink
Product name	EVlink parking
Product or component type	Charging station
Device short name	EVF1
Poles description	1P + N for control circuit 1P + N for power circuit
Mounting mode	Floor-standing
Offer type	Standard
Rated supply voltage	230 V AC 50/60 Hz control circuit 230 V AC 50/60 Hz power circuit
Earthing system	TN TT
Socket-outlet number	2
Socket-outlet type	Right side : T3 / silver plated contacts Left side : T3 / silver plated contacts
Supply current	32 A
Max power	7 kW

Complementary

Control type	2 green illuminated push-button function : unlock flap 2 red push-button function : stop
Local signalling	2 green LED flashing function: on charge 2 green LED function: available 2 orange LED function: reserved 2 red LED function: not operational
Standards	IEC 61851-1 IEC 61851-22
Product certifications	CE CB
Height	1146 mm

Width	413 mm
Depth	220 mm
Product weight	50 kg

Environment

IP degree of protection	IP54 off load conforming to IEC 61851-1 IP54 on load conforming to IEC 61851-1
IK degree of protection	IK10 charging station conforming to IEC 61851-22 IK08 socket-outlet conforming to IEC 61851-22
Ambient air temperature for operation	-30...50 °C conforming to IEC 61851-22
Ambient air temperature for storage	-40...80 °C
Operating altitude	0...2000 m conforming to IEC 61851-22
Relative humidity	0...95 %

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1306 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - Go to CaP for more details Go to CaP for more details
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Available End of Life Information