


# Product data sheet

Specifications



## T2S socket-outlet subassembly 3- Ph IEC - Wallbox spare part

EVP1HSM43

### Main

Range	EVlink
Product Or Component Type	Socket-outlet
Socket-Outlet Type	T2 with shutter
Poles Description	3P + N
[Us] Rated Supply Voltage	380...415 V AC 50/60 Hz
Maximum Supply Current	32 A
Earthing System	Compatible TT Compatible IT with additional isolation transformer on the power supply Compatible TN
Nominal Output Power	22 W 32 A
Range Compatibility	EVlink EVlink Wallbox EVH2 charging station

### Complementary

Material	Plastic
Product Certifications	CE
Height	110 mm
Width	110 mm
Depth	90 mm

### Environment

Ip Degree Of Protection	IP54 conforming to IEC 60529
Ik Degree Of Protection	IK10 conforming to IEC 62262
Ambient Air Temperature For Operation	-30...50 °C
Ambient Air Temperature For Storage	-40...80 °C
Relative Humidity	5...95 %

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15 cm
Package 1 Width	15 cm
Package 1 Length	30 cm
Package 1 Weight	654 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information