



### Main

Range	EVlink
Product or component type	Socket-outlet
Socket-outlet type	T2 with shutter
Poles description	3P + N
[Us] rated supply voltage	380...415 V AC 50/60 Hz
Supply current	32 A
Earthing system	Compatible TT Compatible TN Compatible IT with additional isolation transformer on the power supply
Nominal output power	22 W 32 A
Range compatibility	EVlink wallbox EVH2 charging station

### Complementary

Material	Plastic
Product certifications	CE
Height	110 mm
Width	110 mm
Depth	90 mm

### Environment

IP degree of protection	IP54 conforming to IEC 60529
IK degree of protection	IK10 conforming to IEC 62262
Ambient air temperature for operation	-30...50 °C
Ambient air temperature for storage	-40...80 °C
Relative humidity	5...95 %

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications