



### Main

Range	TeSys
Product name	TeSys GF
Product or component type	Impulse relay
Device short name	GF16
Utilisation category	AC-1
Poles description	2P
Pole contact composition	2 NO
[Ie] rated operational current	16 A AC-1
[Ue] rated operational voltage	250 V AC 50/60 Hz
Permissible short-time rating	320 A ( $\leq 40$ °C) - short time current duration: 1 s 48 A ( $\leq 40$ °C) - short time current duration: 30 s 96 A ( $\leq 40$ °C) - short time current duration: 10 s
Operating position	+/- 90° to vertical plane
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	24 V AC 50/60 Hz
Mounting mode	Clip-on
Mounting support	35 mm symmetrical DIN rail

### Complementary

[Ith] conventional free air thermal current	16 A at $\leq 50$ °C
Average impedance	4 mOhm at 50 Hz - Ith 16 A
[Ui] rated insulation voltage	400 V - conforming to IEC 60947-5-1 400 V - conforming to VDE 0110
[Uimp] rated impulse withstand voltage	4 kV in enclosure
Connections - terminals	Control circuit : screw clamp terminals 1 cable 1.5 mm <sup>2</sup> - cable stiffness: solid - without cable end Control circuit : screw clamp terminals 1 cable 2.5 mm <sup>2</sup> - cable stiffness: flexible - with cable end Control circuit : screw clamp terminals 1 cable 2.5 mm <sup>2</sup> - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 2 cable 1.5 mm <sup>2</sup> - cable stiffness: flexible - with cable end Control circuit : screw clamp terminals 2 cable 1.5 mm <sup>2</sup> - cable stiffness: solid - without cable end

Control circuit : screw clamp terminals 2 cable 2.5 mm<sup>2</sup> - cable stiffness: flexible - without cable end  
 Power circuit : screw clamp terminals 1 cable 0.5...6 mm<sup>2</sup> - cable stiffness: flexible - with cable end  
 Power circuit : screw clamp terminals 1 cable 0.5...6 mm<sup>2</sup> - cable stiffness: flexible - without cable end  
 Power circuit : screw clamp terminals 1 cable 0.5...6 mm<sup>2</sup> - cable stiffness: solid - without cable end  
 Power circuit : screw clamp terminals 2 cable 0.5...4 mm<sup>2</sup> - cable stiffness: flexible - with cable end  
 Power circuit : screw clamp terminals 2 cable 0.5...4 mm<sup>2</sup> - cable stiffness: flexible - without cable end  
 Power circuit : screw clamp terminals 2 cable 0.5...4 mm<sup>2</sup> - cable stiffness: solid - without cable end

Tightening torque	Control circuit : 0.8 N.m - on screw clamp terminals Power circuit : 0.8 N.m - on screw clamp terminals
Operating time	70 ms closing 70 ms opening
Operating rate	<= 900 cyc/h
Control circuit voltage limits	0.85...1.1 Uc at <= 50 °C 50/60 Hz
Impulse duration	>= 70 ms
Average consumption	19 VA for AC network 50 Hz at Uc at 20 °C
Power dissipation per pole	1 W
Mechanical durability	1 Mcycles
Electrical durability	100000 cycles on AC-22 200000 cycles on AC-21
9 mm pitches	2
Height	81 mm
Width	18 mm
Depth	64 mm
Product weight	0.11 kg
Quantity per set	Set of 12

## Environment

Standards	NF C 61-112 IEC 60669-2 IEC 60669-1
IP degree of protection	IP20 conforming to VDE 0106 IP40 in enclosure conforming to VDE 0106
Protective treatment	TC
Ambient air temperature for operation	-20...50 °C
Ambient air temperature for storage	-40...80 °C
Operating altitude	<= 2000 m without derating
Mechanical robustness	Vibrations contactor open 4 Gn, 5...300 Hz Vibrations contactor closed 4 Gn, 5...300 Hz

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0633 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------