



### Main

Range	EVlink
Product name	EVlink parking
Product or component type	Charging station
Device short name	EVW1
Poles description	3P + N for power circuit 1P + N for control circuit
Mounting mode	Wall-mounted
Offer type	Standard
[Us] rated supply voltage	400 V AC 50/60 Hz power circuit 230 V AC 50/60 Hz control circuit
Earthing system	TN TT
Socket number	1
Socket-outlet type	Right side : T2
Supply current	32 A
Nominal output power	22 kW

### Complementary

Control type	1 green illuminated push-button function : unlock flap 1 red push-button function : stop
Local signalling	1 green LED flashing function: on charge 1 green LED function: available 1 orange LED function: reserved 1 red LED function: not operational
Standards	IEC 61851-1 IEC 61851-22
Product certifications	CE CB
Height	620 mm
Width	413 mm

Depth	256 mm
Product weight	33 kg

## Environment

IP degree of protection	IP54 off load conforming to IEC 61851-1 IP54 on load conforming to IEC 61851-1
IK degree of protection	IK10 charging station conforming to IEC 61851-22 IK08 socket-outlet conforming to IEC 61851-22
Ambient air temperature for operation	-30...50 °C conforming to IEC 61851-22
Ambient air temperature for storage	-40...80 °C
Operating altitude	0...2000 m conforming to IEC 61851-22
Relative humidity	0...95 %

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1306 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference contains SVHC above the threshold - Go to CaP for more details <a href="#">Go to CaP for more details</a>
Product environmental profile	Available <a href="#">Product environmental</a>
Product end of life instructions	Available <a href="#">End of life manual</a>