

# Product data sheet

Specifications



## DOL reversing combination starter - TeSys GV2-ME - 1...1.6 A - 380...400V AC

GV2ME06K2Q7

❗ Discontinued

### Main

|                                     |                                                                                                                                                                                                                                      |
|-------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Range                               | TeSys                                                                                                                                                                                                                                |
| Device Short Name                   | GV2ME                                                                                                                                                                                                                                |
| Product Or Component Type           | Motor starter                                                                                                                                                                                                                        |
| Motor Starter Type                  | Reversing                                                                                                                                                                                                                            |
| Poles Description                   | 3P                                                                                                                                                                                                                                   |
| Utilisation Category                | AC-3                                                                                                                                                                                                                                 |
| Motor Power Kw                      | 0.37 kW at 400/415 V AC 50/60 Hz<br>0.55 kW at 400/415 V AC 50/60 Hz<br>0.37 kW at 440 V AC 50/60 Hz<br>0.55 kW at 440 V AC 50/60 Hz<br>0.37 kW at 500 V AC 50/60 Hz<br>0.55 kW at 500 V AC 50/60 Hz<br>0.75 kW at 500 V AC 50/60 Hz |
| [Uc] Control Circuit Voltage        | 380/400 V AC 50/60 Hz                                                                                                                                                                                                                |
| Thermal Protection Adjustment Range | 1...1.6 A                                                                                                                                                                                                                            |
| Magnetic Tripping Current           | 22.5 A                                                                                                                                                                                                                               |

### Complementary

|                    |                                                                                                                                                                                         |
|--------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Device Composition | 1 combination block GV2AF01<br>1 3-pole reversing contactor<br>1 motor circuit breaker type GV2ME                                                                                       |
| Coordination Type  | Type 1                                                                                                                                                                                  |
| Breaking Capacity  | 50 kA Iq at 400/415 V AC 50/60 Hz conforming to IEC 60947-4-1<br>50 kA Iq at 440 V AC 50/60 Hz conforming to IEC 60947-4-1<br>50 kA Iq at 500 V AC 50/60 Hz conforming to IEC 60947-4-1 |
| Net Weight         | 0.46 kg                                                                                                                                                                                 |
| Height             | 152 mm                                                                                                                                                                                  |
| Width              | 45 mm                                                                                                                                                                                   |
| Depth              | 87 mm                                                                                                                                                                                   |

### Packing Units

|                              |     |
|------------------------------|-----|
| Unit Type Of Package 1       | PCE |
| Number Of Units In Package 1 | 1   |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

