



### Main

Range	TeSys
Device short name	GV2ME
Product or component type	Motor starter
Motor starter type	Reversing
Poles description	3P
Utilisation category	AC-3
Motor power kW	3 kW at 400/415 V AC 50/60 Hz 4 kW at 400/415 V AC 50/60 Hz 4 kW at 440 V AC 50/60 Hz 4 kW at 500 V AC 50/60 Hz 5.5 kW at 500 V AC 50/60 Hz
[Uc] control circuit voltage	24 V DC
Thermal protection adjustment range	6...10 A
Magnetic tripping current	138 A

### Complementary

Device composition	1 3-pole reversing contactor 1 combination block GV2AF01 1 motor circuit breaker type GV2ME
Coordination type	Type 1
Breaking capacity	I <sub>q</sub> = 50 kA at 400/415 V AC 50/60 Hz conforming to IEC 60947-4-1 I <sub>q</sub> = 6 kA at 500 V AC 50/60 Hz conforming to IEC 60947-4-1 I <sub>q</sub> = 15 kA at 440 V AC 50/60 Hz conforming to IEC 60947-4-1
Product weight	0.46 kg
Height	152 mm
Width	45 mm
Depth	87 mm

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

## Contractual warranty

Warranty period	18 months
-----------------	-----------