



Main

Range	Easy9
Product or component type	Switch
Device short name	Easy9 switch
Switch application	Distribution
Poles	1P
Utilisation category	AC-22A
Suitability for isolation	Yes

Complementary

[Ie] rated operational current	100 A 230 V 50/60 Hz
[Ue] rated operational voltage	230 V AC 50/60 Hz
[Icm] rated short-circuit making capacity	1.5 kA
[Icw] rated short-time withstand current	1.2 kA 1 s
[Ui] rated insulation voltage	500 V AC 50/60 Hz
[Uimp] rated impulse withstand voltage	4 kV
Control type	Toggle
Local signalling	ON/OFF indication
Contact position indicator	Yes
Mounting mode	Clip-on
Mounting support	DIN rail
9 mm pitches	2
Height	81 mm
Width	18 mm
Depth	66.5 mm
Colour	Grey
Mechanical durability	8500 cycles
Electrical durability	1500 cycles
Connections - terminals	Tunnel type terminal: (top or bottom) 1...50 mm ² rigid

Tunnel type terminal: (top or bottom) 1...35 mm² flexible

Tightening torque	3.5 N.m
-------------------	---------

Environment

Standards	IEC 60947-3
Product certifications	CE
IP degree of protection	IP20 conforming to IEC 60529
Tropicalisation	2
Ambient air temperature for operation	-5...55 °C
Ambient air temperature for storage	-5...70 °C

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1328 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations